




STF G3/4-IG N

Vacuum filter VF / STF / STF-D is delivered as a ready to connect product.

Available spare parts: replacement filter cartridge
Available accessories: mounting bracket



Design data STF G3/4-IG N

Technical data

Attribute	Value
Filter pore size	3.0 µm
Nominal flow rate	42.000 m³/h
Connection	G3/4"-F
Shape	Steel housing

Design data

Attribute	Value
Length L1	158.50 mm
Length L2	5.50 mm
Length L	88.50 mm
Width B1	59.00 mm
Outside diameter D	97.00 mm
Thread G1	G3/4"-F
Thread G2	G3/4"-F

Art.-Nr.: 10.07.01.00007

**Technical data**

Attribute	Value
Max. vacuum	-950 mbar
Filter pore size	3.0 µm
Weight	0.500 kg
Nominal flow rate	42.000 m³/h
Connection	G3/4"-F
Product family	VF

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.01.00007**Ordering Data Spare Parts 10.07.01.00007**

Typ	Item number
Filter insert (round)	FILT-EINS 3 65x70 PAP STF-3/4-IG 10.07.01.00017

**Ordering Data Wear Parts 10.07.01.00007**

Typ	Item number
Filter insert (round)	FILT-EINS 3 65x70 PAP STF-3/4-IG 10.07.01.00017