

Art.-Nr.: 10.07.01.00008




STF G1-1/4-IG N

Vacuum filter VF / STF / STF-D is delivered as a ready to connect product.

Available spare parts: replacement filter cartridge
Available accessories: mounting bracket

Technical data

Attribute	Value
Filter pore size	3.0 µm
Nominal flow rate	96.000 m³/h
Connection	G1-1/4"-F
Shape	Steel housing



Design data STF G1-1/4-IG N

Design data

Attribute	Value
Length L1	191.00 mm
Length L2	17.00 mm
Length L	116.00 mm
Width B1	81.00 mm
Outside diameter D	136.00 mm
Thread G1	G1-1/4"-F
Thread G2	G1-1/4"-F



Art.-Nr.: 10.07.01.00008

**Technical data**

Attribute	Value
Max. vacuum	-950 mbar
Filter pore size	3.0 µm
Weight	1.000 kg
Nominal flow rate	96.000 m³/h
Connection	G1-1/4"-F
Product family	VF

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.01.00008**Ordering Data Spare Parts 10.07.01.00008**

Typ		Item number
Filter insert (round)	FILT-EINS 3 98x70 PAP STF-1-1/4-IGN	10.07.01.00018

**Ordering Data Wear Parts 10.07.01.00008**

Typ		Item number
Filter insert (round)	FILT-EINS 3 98x70 PAP STF-1-1/4-IGN	10.07.01.00018