


Art.-Nr.: 10.07.01.00010



STF G2-1/2-IG N

Vacuum filter VF / STF / STF-D is delivered as a ready to connect product.

Available spare parts: replacement filter cartridge
Available accessories: mounting bracket



Design data STF G2-1/2-IG N

Technical data

Attribute	Value
Filter pore size	3.0 µm
Nominal flow rate	360.000 m³/h
Connection	G2-1/2"-F
Shape	Steel housing

Design data

Attribute	Value
Length L1	490.00 mm
Length L2	12.00 mm
Length L	250.00 mm
Width B1	123.00 mm
Outside diameter D	200.00 mm
Thread G1	G2-1/2"-F
Thread G2	G2-1/2"-F



Art.-Nr.: 10.07.01.00010

**Technical data**

Attribute	Value
Max. vacuum	-950 mbar
Filter pore size	3.0 µm
Weight	4.300 kg
Nominal flow rate	360.000 m³/h
Connection	G2-1/2"-F
Product family	VF

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.01.00010**Ordering Data Spare Parts 10.07.01.00010**

Typ	Item number
Filter insert (round)	FILT-EINS 3 150x222 PAP STF-2-1/2-IG 10.07.01.00020

**Ordering Data Wear Parts 10.07.01.00010**

Typ	Item number
Filter insert (round)	FILT-EINS 3 150x222 PAP STF-2-1/2-IG 10.07.01.00020