




VFT G1/8-IG 100

Vacuum filter VFT is delivered as a ready-to-connect product.

Available spare parts: filter cartridge (filter insert)

Available accessories: filter holder



Design data VFT G1/8-IG 100

Technical data

Attribute	Value
Filter pore size	100.0 µm
Nominal flow rate	3.000 m³/h
Connection	G1/8"-F
Shape	short filter insert

Design data

Attribute	Value
Length L	76.00 mm
Height H1	50.00 mm
Height H	60.00 mm
Outside diameter D	48.00 mm
Thread G1	G1/8"-F

Vacuum cup filter
VFT G1/8-IG 100



Art.-Nr.: 10.07.01.00117



Technical data

Attribute	Value
Overpressure (max.) at 25° C	7.0 bar
Overpressure (max.) at 50° C	5.0 bar
Max. vacuum	-990 mbar
Filter pore size	100.0 µm
Weight	49.0 g
Nominal flow rate	3.000 m³/h
Connection	G1/8"-F
Product family	VFT



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.01.00117



Ordering Data Spare Parts 10.07.01.00117

Typ		Item number
Filter insert (round)	FILT-EINS 100 25x37 A2 VFT-1/8+1/4	10.07.01.00132
Filter holder	HTR-FIL 25 WI VFT1/8-1/2	10.07.01.00228
Sealing element	DR 37-33x3 NBR	10.07.01.00154



WWW.SCHMALZ.COM/10.07.01.00117