



Technical data


Attribute	Value
Filter pore size	80.0 µm
Nominal flow rate	14.700 m³/h
Connection	G3/8"-F
Shape	Long filter insert

VFT G3/8-IG 80

Vacuum filter VFT is delivered as a ready-to-connect product.

Available spare parts: filter cartridge (filter insert)

Available accessories: filter holder



Design data

Attribute	Value
Length L	77.20 mm
Height H1	88.00 mm
Height H	101.00 mm
Outside diameter D	48.50 mm
Thread G1	G3/8"-F

Design data VFT G3/8-IG 80

Vacuum cup filter
VFT G3/8-IG 80



Art.-Nr.: 10.07.01.00122



Technical data

Attribute	Value
Overpressure (max.) at 25° C	7.0 bar
Overpressure (max.) at 50° C	5.0 bar
Max. vacuum	-990 mbar
Filter pore size	80.0 µm
Weight	79.0 g
Nominal flow rate	14.700 m³/h
Connection	G3/8"-F
Product family	VFT



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.01.00122



Ordering Data Spare Parts 10.07.01.00122

Typ		Item number
Filter insert (round)	FILT-EINS 80 25x71 PE VFT-3/8-1/2	10.07.01.00143
Filter holder	HTR-FIL 25 WI VFT1/8-1/2	10.07.01.00228
Sealing element	DR 37-33x3 NBR	10.07.01.00154



WWW.SCHMALZ.COM/10.07.01.00122