



VFT G3/4-IG 80

Vacuum filter VFT is delivered as a ready-to-connect product.

Available spare parts: filter cartridge (filter insert)


Available accessories: filter holder

Technical data

Attribute	Value
Filter pore size	80.0 µm
Nominal flow rate	36.000 m³/h
Connection	G3/4"-F
Shape	Long filter insert

Design data

Attribute	Value
Length L	90.50 mm
Height H1	118.00 mm
Height H	136.50 mm
Outside diameter D	75.00 mm
Thread G1	G3/4"-F



Design data VFT G3/4-IG 80

Vacuum cup filter
VFT G3/4-IG 80



Art.-Nr.: 10.07.01.00128



Technical data

Attribute	Value
Overpressure (max.) at 25° C	7.0 bar
Overpressure (max.) at 50° C	5.0 bar
Max. vacuum	-990 mbar
Filter pore size	80.0 µm
Weight	164.0 g
Nominal flow rate	36.000 m³/h
Connection	G3/4" -F
Product family	VFT



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.01.00128



Ordering Data Spare Parts 10.07.01.00128

Typ		Item number
Filter insert (round)	FILT-EINS 80 39x89 PE VFT-3/4	10.07.01.00145
Filter holder	HTR-FIL 2S WI VFT3/4	10.07.01.00229
Sealing element	DR 57-51x3.2 NBR	10.07.01.00155



WWW.SCHMALZ.COM/10.07.01.00128