




Technical data

Attribute	Value
Filter pore size	50.0 µm
Connection	Hose 6/4 with Cap nut

VFI CN6/4 50

Inline filter VFI is delivered as a ready-to-connect product.

Available spare parts: filter cartridge (filter insert)



Design data

Attribute	Value
Length L	61.00 mm
Outside diameter D	16.00 mm
Internal diameter d	6.00 mm

Design data VFI CN6/4 50



Art.-Nr.: 10.07.01.00241

**Technical data**

Attribute	Value
Overpressure (max.) at 25° C	7.0 bar
Overpressure (max.) at 50° C	5.0 bar
Max. vacuum	-990 mbar
Filter pore size	50.0 µm
Weight	6.00 g
Nominal flow rate	1.920 m³/h
Connection	Hose 6/4 with Cap nut
Product family	VFI

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.01.00241**Ordering Data Accessories 10.07.01.00241**

Typ		Item number
Filter insert (round)	FILT-EINS 50 10x21 VFI	10.07.01.00244

**Ordering Data Spare Parts 10.07.01.00241**

Typ		Item number
Filter insert (round)	FILT-EINS 50 10x21 VFI	10.07.01.00244

