

Vacuum filter (inline)

## VFI CN8/6 50

Art.-Nr.: 10.07.01.00245



### Technical data

Filter pore size	50.0 µm
Connection	Hose 8/6 with Cap nut


VFI CN8/6 50

Inline filter VFI is delivered as a ready-to-connect product.

Available spare parts: filter cartridge (filter insert)

### Design data

Length L	68.00 mm
Outside diameter D	23.00 mm
Internal diameter d	8.00 mm



Design data VFI CN8/6 50



[WWW.SCHMALZ.COM/10.07.01.00245](http://WWW.SCHMALZ.COM/10.07.01.00245)

1

Vacuum filter (inline)

## VFI CN8/6 50



Art.-Nr.: 10.07.01.00245



### Technical data

Overpressure (max.) at 25° C	7.0 bar
Overpressure (max.) at 50° C	5.0 bar
Max. vacuum	-990 mbar
Filter pore size	50.0 µm
Weight	10.00 g
Nominal flow rate	3.960 m <sup>3</sup> /h
Connection	Hose 8/6 with Cap nut
Product family	VFI



### Ordering Data Spare Parts 10.07.01.00245

Typ		Item number
Filter insert (round)	FILT-EINS 50 16x23 VFI	10.07.01.00248



### Ordering Data Wear Parts 10.07.01.00245

Typ		Item number
Filter insert (round)	FILT-EINS 50 16x23 VFI	10.07.01.00248



[WWW.SCHMALZ.COM/10.07.01.00245](http://WWW.SCHMALZ.COM/10.07.01.00245)