

Art.-Nr.: 10.07.01.00259



STF 60 P 4.5 SSD

Vacuum filter VF / STF / STF-D is delivered as a ready to connect product.


Available spare parts: replacement filter cartridge
Available accessories: mounting bracket

Technical data

Attribute	Value
Filter pore size	3.0 µm
Nominal flow rate	270.000 m³/h
Connection	Ø60mm
Shape	Piclon housing
Additional equipment	Hose clamps SSD

Design data

Attribute	Value
Length L1	658.00 mm
Length L2	304.00 mm
Length L	355.00 mm
Width B1	221.00 mm
Width B2	112.00 mm
Height H	218.00 mm
Outside diameter D1	198.0 mm
Outside diameter D2	60.0 mm
Outside diameter D	170.00 mm
Internal diameter d	8.50 mm
Hole spacing X1	192.0 mm
D3	60.0 mm



Design data STF 60 P 4.5 SSD



Art.-Nr.: 10.07.01.00259

**Technical data**

Attribute	Value
Max. vacuum	-500 mbar
Filter pore size	3.0 µm
Weight	2.000 kg
Nominal flow rate	270.000 m³/h
Connection	Ø60mm
Product family	VF

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.01.00259**Ordering Data Spare Parts 10.07.01.00259**

Typ	Item number
Filter insert (round)	FILT-EINS 3 124x320 PAP STF-Picl-4.5 10.07.01.00060

