

Dust filter

STF 60 P 6.0 SSD



Art.-Nr.: 10.07.01.00260




Technical data

Filter pore size	3.0 µm
Nominal flow rate	360.000 m ³ /h
Connection	Ø60mm
Shape	Piclon housing
Additional equipment	Hose clamps SSD

STF 60 P 6.0 SSD

Vacuum filter VF / STF / STF-D is delivered as a ready to connect product.

Available spare parts: replacement filter cartridge
Available accessories: mounting bracket



Design data

Length L1	741.00 mm
Length L2	344.00 mm
Length L	390.00 mm
Width B1	265.00 mm
Width B2	142.00 mm
Height H	253.00 mm
Outside diameter D1	229.0 mm
Outside diameter D2	60.0 mm
Outside diameter D	200.00 mm
Internal diameter d	8.50 mm
Hole spacing X1	220.0 mm
D3	60.0 mm

Design data STF 60 P 6.0 SSD



WWW.SCHMALZ.COM/10.07.01.00260

1

Dust filter

STF 60 P 6.0 SSD



Art.-Nr.: 10.07.01.00260



Technical data

Max. vacuum	-500 mbar
Filter pore size	3.0 µm
Weight	2.400 kg
Nominal flow rate	360.000 m³/h
Connection	Ø60mm
Product family	VF



Ordering Data Spare Parts 10.07.01.00260

Typ		Item number
Filter insert (round)	FILT-EINS 3 149x361 PAP STF-Picl-6	10.07.01.00054
Hose clamp	SSD 60-68 ST-VZ	10.07.10.00017



WWW.SCHMALZ.COM/10.07.01.00260