

Dust filter (with pressure monitor)

STF-D 60 P 6.0 F SSD



Art.-Nr.: 10.07.01.00262



STF-D 60 P 6.0 F SSD

Vacuum filter VF / STF / STF-D is delivered as a ready to connect product.


Available spare parts: replacement filter cartridge
Available accessories: mounting bracket

Technical data

Attribute	Value
Filter pore size	3.0 µm
Nominal flow rate	360.000 m³/h
Additional function	Filter monitoring
Connection	Ø60mm
Shape	Piclon housing
Additional equipment	Hose clamps SSD

Design data

Attribute	Value
Length L1	741.00 mm
Length L2	351.00 mm
Length L	390.00 mm
Width B1	265.00 mm
Width B2	142.00 mm
Height H	253.00 mm
Outside diameter D1	229.0 mm
Outside diameter D2	60.0 mm
Outside diameter D	200.00 mm
Internal diameter d	8.50 mm
Hole spacing X1	220.0 mm
D3	60.0 mm



Design data STF-D 60 P 6.0 F SSD



WWW.SCHMALZ.COM/10.07.01.00262

Dust filter (with pressure monitor)

STF-D 60 P 6.0 F SSD



Art.-Nr.: 10.07.01.00262



Technical data

Attribute	Value
Max. vacuum	-500 mbar
Filter pore size	3.0 µm
Weight	2.400 kg
Nominal flow rate	360.000 m³/h
Connection	Ø60mm
Product family	VF



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.01.00262



Ordering Data Spare Parts 10.07.01.00262

Typ		Item number
Filter insert (round)	FILT-EINS 3 149x361 PAP STF-Picl-6	10.07.01.00054
Differential pressure monitor	DDW 10...50 250V-AC/6	21.01.06.00011
Hose clamp	SSD 60-68 ST-VZ	10.07.10.00017



Ordering Data Wear Parts 10.07.01.00262

Typ		Item number
Filter insert (round)	FILT-EINS 3 149x361 PAP STF-Picl-6	10.07.01.00054



WWW.SCHMALZ.COM/10.07.01.00262