



STF 75 P 8.0 SSD


Technical data

Attribute	Value
Filter pore size	3.0 µm
Nominal flow rate	480.000 m³/h
Connection	Ø75mm
Shape	Piclon housing
Additional equipment	Hose clamps SSD

Vacuum filter VF / STF / STF-D is delivered as a ready to connect product.

Available spare parts: replacement filter cartridge

Available accessories: mounting bracket



Design data STF 75 P 8.0 SSD

Design data

Attribute	Value
Length L1	579.00 mm
Length L2	359.00 mm
Length L	439.00 mm
Width B1	300.00 mm
Width B2	168.00 mm
Height H	250.60 mm
Outside diameter D1	240.0 mm
Outside diameter D2	75.0 mm
Outside diameter D	228.00 mm
Internal diameter d	8.50 mm

Art.-Nr.: 10.07.01.00263

**Technical data**

Attribute	Value
Max. vacuum	-500 mbar
Filter pore size	3.0 µm
Weight	2.600 kg
Nominal flow rate	480.000 m³/h
Connection	Ø75mm
Product family	VF

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.01.00263**Ordering Data Spare Parts 10.07.01.00263**

Typ	Item number
Filter insert (round)	FILT-EINS 3 159x376 STF-Picl-8 10.07.01.00079

