

Dust filter (with pressure monitor)

STF-D 60 P 4.5 F SSD



Art.-Nr.: 10.07.01.00266



STF-D 60 P 4.5 F SSD

Vacuum filter VF / STF / STF-D is delivered as a ready to connect product.


Available spare parts: replacement filter cartridge
Available accessories: mounting bracket

Technical data

Attribute	Value
Filter pore size	3.0 µm
Nominal flow rate	270.000 m³/h
Additional function	Filter monitoring
Connection	Ø60mm
Shape	Piclon housing
Additional equipment	Hose clamps SSD

Design data

Attribute	Value
Length L1	658.00 mm
Length L2	303.00 mm
Length L	355.00 mm
Width B1	221.00 mm
Width B2	112.00 mm
Height H	218.00 mm
Outside diameter D1	198.0 mm
Outside diameter D2	60.0 mm
Outside diameter D	170.00 mm
Internal diameter d	8.50 mm



Design data STF-D 60 P 4.5 F SSD



WWW.SCHMALZ.COM/10.07.01.00266

Dust filter (with pressure monitor)

STF-D 60 P 4.5 F SSD



Art.-Nr.: 10.07.01.00266



Technical data

Attribute	Value
Max. vacuum	-500 mbar
Filter pore size	3.0 µm
Weight	2.100 kg
Nominal flow rate	270.000 m³/h
Connection	Ø60mm
Product family	VF



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.01.00266



Ordering Data Spare Parts 10.07.01.00266

Typ		Item number
Filter insert (round)	FILT-EINS 3 124x320 PAP STF-Picl-4.5	10.07.01.00060
Differential pressure monitor	DDW 10...50 250V-AC/6	21.01.06.00011
Hose clamp	SSD 60-68 ST-VZ	10.07.10.00017



Ordering Data Wear Parts 10.07.01.00266

Typ		Item number
Filter insert (round)	FILT-EINS 122x320 PAP STF-Picl-4.5	11.04.03.10086
Filter insert (round)	FILT-EINS 3 124x320 PAP STF-Picl-4.5	10.07.01.00060



WWW.SCHMALZ.COM/10.07.01.00266