

Vacuum filter (inline)

VFI 6/4 50

Art.-Nr.: 10.07.01.00328




Technical data

Filter pore size	50.0 µm
Connection	Hose 6/4

VFI 6/4 50

Inline filter VFI is delivered as a ready-to-connect product.

Available spare parts: filter cartridge (filter insert)



Design data

Length L	69.00 mm
Outside diameter D	25.00 mm
Internal diameter d	6.00 mm

Design data VFI 6/4 50



WWW.SCHMALZ.COM/10.07.01.00328

Art.-Nr.: 10.07.01.00328



Technical data

Overpressure (max.) at 25° C	7.0 bar
Overpressure (max.) at 50° C	5.0 bar
Max. vacuum	-990 mbar
Filter pore size	50.0 µm
Weight	16.50 g
Nominal flow rate	3.960 m³/h
Connection	Hose 6/4
Product family	VFI



Ordering Data Accessories 10.07.01.00328

Typ		Item number
Filter insert (round)	FILT-EINS 50 16x23 VFI	10.07.01.00248



Ordering Data Spare Parts 10.07.01.00328

Typ		Item number
Filter insert (round)	FILT-EINS 50 16x23 VFI	10.07.01.00248



Ordering Data Wear Parts 10.07.01.00328

Typ		Item number
Filter insert (round)	FILT-EINS 50 16x23 VFI	10.07.01.00248

