



STF 110 P 12.0 SSB

Vacuum filter VF / STF / STF-D is delivered as a ready to connect product.


Available spare parts: replacement filter cartridge
Available accessories: mounting bracket

Technical data

Attribute	Value
Filter pore size	3.0 µm
Nominal flow rate	720.000 m³/h
Connection	Ø110mm
Shape	Piclon housing
Additional equipment	Hose clamps SSB

Design data

Attribute	Value
Length L1	829.00 mm
Length L2	384.00 mm
Length L	445.00 mm
Width B1	369.00 mm
Width B2	214.00 mm
Height H	335.00 mm
Outside diameter D1	288.0 mm
Outside diameter D2	109.0 mm
Outside diameter D	264.00 mm
Internal diameter d	8.50 mm



Design data STF 110 P 12.0 SSB

Art.-Nr.: 10.07.01.00360

**Technical data**

Attribute	Value
Max. vacuum	-500 mbar
Filter pore size	3.0 µm
Weight	3.800 kg
Nominal flow rate	720.000 m³/h
Connection	Ø110mm
Product family	VF

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.01.00360**Ordering Data Wear Parts 10.07.01.00360**

Typ	Item number
Filter insert (round)	FILT-EINS 194x401 PAP STF-Picl-12 10.07.01.00361

