

Art.-Nr.: 10.07.01.00384


**Technical data**

Nominal flow rate	480.000 m ³ /h
Connection	Ø60mm
Shape	Piclon housing

STF 60 P 8.0

Vacuum filter VF / STF / STF-D is delivered as a ready to connect product.

Available spare parts: replacement filter cartridge
 Available accessories: mounting bracket

**Design data**

Length L1	561.00 mm
Length L2	359.00 mm
Length L	423.00 mm
Width B1	286.00 mm
Width B2	155.00 mm
Height H	250.50 mm
Outside diameter D1	248.0 mm
Outside diameter D2	60.0 mm
Outside diameter D	228.00 mm
Internal diameter d	8.50 mm
Hole spacing X1	240.0 mm
D3	60.0 mm

Design data STF 60 P 8.0



Dust filter

STF 60 P 8.0



Art.-Nr.: 10.07.01.00384



Technical data

Weight	3.270 kg
Nominal flow rate	480.000 m ³ /h
Connection	Ø60mm
Product family	VF



Ordering Data Spare Parts 10.07.01.00384

Typ		Item number
Filter insert (round)	FILT-EINS 3 159x376 STF-Picl-8	10.07.01.00079



WWW.SCHMALZ.COM/10.07.01.00384