

Art.-Nr.: 10.07.01.00398


**Technical data**

Filter pore size	3.0 µm
Nominal flow rate	270.000 m <sup>3</sup> /h
Connection	Ø40mm
Shape	Piclon housing
Additional equipment	Hose clamps SSD

STF 40 P 4.5 SSD

Vacuum filter VF / STF / STF-D is delivered as a ready to connect product.

Available spare parts: replacement filter cartridge  
 Available accessories: mounting bracket

**Design data**

Length L1	658.00 mm
Length L2	304.00 mm
Length L	355.00 mm
Width B1	221.00 mm
Width B2	112.00 mm
Height H	218.00 mm
Outside diameter D1	198.0 mm
Outside diameter D2	40.0 mm
Outside diameter D	170.00 mm
Internal diameter d	8.50 mm
Hole spacing X1	192.0 mm
D3	40.0 mm

Design data STF 40 P 4.5 SSD



Dust filter

## STF 40 P 4.5 SSD



Art.-Nr.: 10.07.01.00398



### Technical data

Max. vacuum	-500 mbar
Filter pore size	3.0 µm
Weight	2.000 kg
Nominal flow rate	270.000 m³/h
Connection	Ø40mm
Product family	VF



[WWW.SCHMALZ.COM/10.07.01.00398](http://WWW.SCHMALZ.COM/10.07.01.00398)