

Dust filter

STF 75 P 12.0 SSD



Art.-Nr.: 10.07.01.00399




Technical data

Filter pore size	3.0 µm
Nominal flow rate	720.000 m ³ /h
Connection	Ø75mm
Shape	Piclon housing
Additional equipment	Hose clamps SSD

STF 75 P 12.0 SSD

Vacuum filter VF / STF / STF-D is delivered as a ready to connect product.

Available spare parts: replacement filter cartridge
Available accessories: mounting bracket



Design data

Length L1	829.00 mm
Length L2	384.00 mm
Length L	445.00 mm
Width B1	369.00 mm
Width B2	214.00 mm
Height H	335.00 mm
Outside diameter D1	288.0 mm
Outside diameter D2	75.0 mm
Outside diameter D	264.00 mm
Internal diameter d	8.50 mm
Hole spacing X1	280.0 mm
D3	75.0 mm

Design data STF 75 P 12.0 SSD



WWW.SCHMALZ.COM/10.07.01.00399

1

Dust filter

STF 75 P 12.0 SSD



Art.-Nr.: 10.07.01.00399



Technical data

Max. vacuum	-500 mbar
Filter pore size	3.0 µm
Weight	4.000 kg
Nominal flow rate	720.000 m³/h
Connection	Ø75mm
Product family	VF



Ordering Data Spare Parts 10.07.01.00399

Typ		Item number
Filter insert (round)	FILT-EINS 194x401 PAP STF-Picl-12	10.07.01.00361



WWW.SCHMALZ.COM/10.07.01.00399