

Dust filter

STF 100 P 15.0 SSD



Art.-Nr.: 10.07.01.00400



STF 100 P 15.0 SSD


Vacuum filter VF / STF / STF-D is delivered as a ready to connect product.

Available spare parts: replacement filter cartridge
Available accessories: mounting bracket

Technical data

Attribute	Value
Filter pore size	3.0 µm
Nominal flow rate	900.000 m³/h
Connection	Ø100mm
Shape	Piclon housing
Additional equipment	Hose clamps SSD

Design data



Attribute	Value
Length L1	829.00 mm
Length L2	384.00 mm
Length L	440.50 mm
Width B1	362.50 mm
Width B2	190.00 mm
Height H	334.00 mm
Outside diameter D1	317.6 mm
Outside diameter D2	100.0 mm
Outside diameter D	293.00 mm
Internal diameter d	8.50 mm
Hole spacing X1	315.0 mm
D3	100.0 mm

Design data STF 100 P 15.0 SSD



WWW.SCHMALZ.COM/10.07.01.00400

Dust filter

STF 100 P 15.0 SSD



Art.-Nr.: 10.07.01.00400



Technical data

Attribute	Value
Max. vacuum	-500 mbar
Filter pore size	3.0 µm
Nominal flow rate	900.000 m³/h
Connection	Ø100mm
Product family	VF



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.01.00400



Ordering Data Spare Parts 10.07.01.00400

Typ		Item number
Filter insert (round)	FILT-EINS 220x393 PAP STF-Pic1-15	10.07.01.00362



WWW.SCHMALZ.COM/10.07.01.00400