

Art.-Nr.: 10.07.01.00401



STF 100 P 24.0 SSD

Vacuum filter VF / STF / STF-D is delivered as a ready to connect product.


Available spare parts: replacement filter cartridge
Available accessories: mounting bracket

Technical data

Attribute	Value
Filter pore size	3.0 µm
Nominal flow rate	1,440.000 m³/h
Connection	Ø100mm
Shape	Piclon housing
Additional equipment	Hose clamps SSD

Design data

Attribute	Value
Length L1	1,080.00 mm
Length L2	500.00 mm
Length L	580.30 mm
Width B1	406.00 mm
Width B2	193.50 mm
Height H	382.00 mm
Outside diameter D1	353.0 mm
Outside diameter D2	100.0 mm
Outside diameter D	321.00 mm
Internal diameter d	8.50 mm



Design data STF 100 P 24.0 SSD



Dust filter

STF 100 P 24.0 SSD



Art.-Nr.: 10.07.01.00401



Technical data

Attribute	Value
Filter pore size	3.0 µm
Nominal flow rate	1,440.000 m³/h
Connection	Ø100mm
Product family	VF



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.01.00401



Ordering Data Spare Parts 10.07.01.00401

Typ		Item number
Filter insert (round)	FILT-EINS 3 240x539 PAP STF-Picl-24	10.07.01.00083



WWW.SCHMALZ.COM/10.07.01.00401