

Art.-Nr.: 10.07.02.00057



VAM-D 30x30 VP10 G1/8-AG SET

Electronic manometer VAM-D is delivered as a ready-to-connect product.


Available accessories: mounting bracket, mounting frame

Technical data

Attribute	Value
Measuring range [bar]	-1,0 ... 10,0 bar
Length L	30.00 mm
Width B	30.00 mm
Vacuum connection	G1/8"-M

Design data

Attribute	Value
Length L	30.00 mm
Width B	30.00 mm
Height H1	37.00 mm
Height H	21.80 mm
Thread G1	G1/8"-M
Thread length LG1	5.6 mm
Thread G2	M5-F
Thread length LG2	9.3 mm
Key width SW1	12.0 mm
Thread length LG4	4.0 mm



Design data VAM-D 30x30 VP10 G1/8-AG SET

VAM-D 30x30 VP10 G1/8-AG SET

Art.-Nr.: 10.07.02.00057



Technical data

Attribute	Value
Protection type IP	IP 40/65 (with hose)
Max. overpressure safety	3.0 bar
Weight	40.00 g
Measured value display	3-digit 7-segment LED
Measured medium	Non-aggressive gases; dry, oil-free air
Repeatability	± 1% of full-scale value
Measuring range [bar]	-1,0 ... 10,0 bar
Operating temperature	0 ... 50 °C
Product family	VAM-D



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.02.00057

Ordering Data Accessories 10.07.02.00057

Typ		Item number
Mounting bracket	BEF-WIN 13x50x31 1.6 VS	10.06.02.00425
Mounting frame	EINB-RAx8.5x30 VS	10.06.02.00427

