

Art.-Nr.: 10.07.04.00002




DI-SCHN 8 MOS EPDM-20

Sealing cord DI-SCHN is delivered in the desired length. Accounting unit 1 m.

Technical data

Attribute	Value
Material hardness [Shore A]	20.0 Shore A
Sealing material	EPDM
Outside diameter D	8.00 mm



Design data DI-SCHN 8 MOS EPDM-20

Design data

Attribute	Value
Outside diameter D	8.00 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 E3

**Technical data**

Attribute	Value
Min. bending radius	10.0 mm
Product family	DI-SCHN



Sealing cord

DI-SCHN 8 MOS EPDM-20



Art.-Nr.: 10.07.04.00002



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.04.00002



WWW.SCHMALZ.COM/10.07.04.00002