

Art.-Nr.: 10.07.04.00006



Technical data

Attribute	Value
Material hardness [Shore A]	20.0 Shore A
Sealing material	EPDM
Width B	10.00 mm
Height H	6.00 mm


DI-PROF 10x6 MOS EPDM-20

Sealing profile DI-PROF is delivered in the desired length. Accounting unit 1 m.

Design data

Attribute	Value
Width B	10.00 mm
Height H	6.00 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 E3



Design data DI-PROF 10x6 MOS EPDM-20



Sealing profile (meter)

DI-PROF 10x6 MOS EPDM-20



Art.-Nr.: 10.07.04.00006



Technical data

Attribute	Value
Material hardness [Shore A]	20.0 Shore A
Weight	27.8 g
Sealing material	EPDM
Recommended slot width x slot depth [mm]	11x3
Product family	DI-PROF



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.04.00006



WWW.SCHMALZ.COM/10.07.04.00006