


Sealing profile (meter)

## DI-PROF 25x20 MOS EPDM-20



Art.-Nr.: 10.07.04.00007



### Technical data

Material hardness [Shore A]	20.0 Shore A
Sealing material	EPDM
Material type	Foam rubber
Width B	25.00 mm
Height H	20.00 mm


DI-PROF 25x20 MOS EPDM-20

Sealing profile DI-PROF is delivered in the desired length. Accounting unit 1 m.

### Design data

Width B	25.00 mm
Height H	20.00 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 E3



Design data DI-PROF 25x20 MOS EPDM-20



[WWW.SCHMALZ.COM/10.07.04.00007](http://WWW.SCHMALZ.COM/10.07.04.00007)

1

Sealing profile (meter)

## DI-PROF 25x20 MOS EPDM-20



Art.-Nr.: 10.07.04.00007



### Technical data

Material hardness [Shore A]	20.0 Shore A
Weight	150.00 g
Sealing material	EPDM
Recommended slot width x slot depth [mm]	26x10
Product family	DI-PROF



[WWW.SCHMALZ.COM/10.07.04.00007](http://WWW.SCHMALZ.COM/10.07.04.00007)