


Art.-Nr.: 10.07.04.00010




Technical data

Attribute	Value
Material hardness [Shore A]	20.0 Shore A
Sealing material	EPDM
Width B	10.00 mm
Height H	20.00 mm
Form	half-round

DI-PROF 10x20 MOS EPDM-20 HR

Sealing profile DI-PROF is delivered in the desired length. Accounting unit 1 m.



Design data

Attribute	Value
Width B	10.00 mm
Height H	20.00 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 E3

Design data DI-PROF 10x20 MOS EPDM-20 HR



Sealing profile (meter)

DI-PROF 10x20 MOS EPDM-20 HR



Art.-Nr.: 10.07.04.00010



Technical data

Attribute	Value
Material hardness [Shore A]	20.0 Shore A
Weight	89.00 g
Sealing material	EPDM
Recommended slot width x slot depth [mm]	11x10
Product family	DI-PROF



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.04.00010



WWW.SCHMALZ.COM/10.07.04.00010