

Art.-Nr.: 10.07.04.00011



DI-PROF 12x17 MOS EPDM-20 HR

Sealing profile DI-PROF is delivered in the desired length. Accounting unit 1 m.


Technical data

Attribute	Value
Material hardness [Shore A]	20.0 Shore A
Sealing material	EPDM
Width B	12.00 mm
Height H	17.00 mm
Form	half-round

Design data

Attribute	Value
Width B	12.00 mm
Height H	17.00 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 E3



Design data DI-PROF 12x17 MOS EPDM-20 HR



Sealing profile (meter)

DI-PROF 12x17 MOS EPDM-20 HR



Art.-Nr.: 10.07.04.00011



Technical data

Attribute	Value
Material hardness [Shore A]	20.0 Shore A
Weight	72.0 g
Sealing material	EPDM
Recommended slot width x slot depth [mm]	13x10
Product family	DI-PROF



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.04.00011



WWW.SCHMALZ.COM/10.07.04.00011