

Sealing profile (meter)

DI-PROF 20x15 2K-SWG NK-20/55



Art.-Nr.: 10.07.04.00040




Technical data

| | |
|-----------------------------|-------------------|
| Material hardness [Shore A] | 20.0 Shore A |
| Sealing material | Natural Rubber NK |
| Width B | 20.00 mm |
| Height H | 15.00 mm |

DI-PROF 20x15 2K-SWG NK-20/55

Sealing profile DI-PROF is delivered in the desired length. Accounting unit 1 m.



Design data

| | |
|-----------|----------|
| Width B1 | 22.00 mm |
| Width B2 | 2.00 mm |
| Width B | 20.00 mm |
| Height H1 | 33.00 mm |
| Height H2 | 6.00 mm |
| Height H | 15.00 mm |
| Width B3 | 16.00 mm |
| Height H3 | 6.00 mm |
| Height H4 | 12.00 mm |

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 E3

Design data DI-PROF 20x15 2K-SWG NK-20/55



Technical data

| | |
|-----------------------------|-------------------|
| Material hardness [Shore A] | 20.0 Shore A |
| Weight | 411.50 g |
| Sealing material | Natural Rubber NK |
| Product family | DI-PROF |



WWW.SCHMALZ.COM/10.07.04.00040

1