




Technical data

Attribute	Value
Material hardness [Shore A]	20.0 Shore A
Sealing material	Natural Rubber NK
Width B	30.00 mm
Height H	25.00 mm

DI-PROF 30x25 2K-SWG NK-20/55

Sealing profile DI-PROF is delivered in the desired length. Accounting unit 1 m.



Design data

Attribute	Value
Width B1	32.00 mm
Width B2	2.00 mm
Width B	30.00 mm
Height H1	53.00 mm
Height H2	8.00 mm
Height H	25.00 mm
Width B3	24.00 mm
Height H3	10.00 mm
Height H4	17.00 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 E3

Design data DI-PROF 30x25 2K-SWG NK-20/55

Sealing profile (meter)

DI-PROF 30x25 2K-SWG NK-20/55



Art.-Nr.: 10.07.04.00041



Technical data

Attribute	Value
Material hardness [Shore A]	20.0 Shore A
Weight	1,201.20 g
Sealing material	Natural Rubber NK
Product family	DI-PROF



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.04.00041



WWW.SCHMALZ.COM/10.07.04.00041