


Art.-Nr.: 10.07.06.00241



Technical data

Attribute	Value
Operating temperature	-5 ... 130 °C
Thread G1	G1/4"-F
Thread G2	M6-M

FLK-HD G1/4-IG



Design data

Attribute	Value
Length L	31.60 mm
Outside diameter D	69.00 mm
Nominal diameter dn	9.00 mm
Internal diameter d	6.40 mm
Thread G1	G1/4"-F
Thread length LG1	12.0 mm
Thread G2	M6-M
Thread length LG2	10.5 mm
Key width SW1	17.0 mm
Spanner size SW2	5.0 mm

Design data FLK-HD G1/4-IG



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.06.00241



WWW.SCHMALZ.COM/10.07.06.00241