


Art.-Nr.: 10.07.06.00500




## Technical data

Additional function	Active blow-off
Connection 1	Bolt with slot Ø19mm
Suction cup connection	NPT3/8-M
Vacuum connection	G 1/8"-F
Shape	integrated nozzle

HT-SG A2 I 10 31 NPT3/8-AG AB

The holders for suction cups HT-SG I are delivered as a ready-to-connect product.

Available accessories: push-in fittings STV-GE



## Design data

Length L1	72.50 mm
Length L2	60.80 mm
Length L	39.30 mm
Width B1	73.00 mm
Width B2	32.00 mm
Width B	31.00 mm
Height H1	52.00 mm
Height H	24.50 mm
Outside diameter D	19.00 mm
Thread G2	NPT3/8-M
Thread length LG2	15.0 mm
Length L3	11.70 mm
Thread G4	G 1/8"-F
Thread G3	G 1/8"-F

Design data HT-SG A2 I 10 31 NPT3/8-AG AB



Holder tooling suction Cup

# HT-SG A2 I 10 31 NPT3/8-AG AB



Art.-Nr.: 10.07.06.00500



## Technical data

Weight	136.00 g
Product family	HT-SG-I



## Ordering Data Accessories 10.07.06.00500

Typ		Item number
Plug union, straight	STV-GE G1/8-AG 6	10.08.02.00204
Plug union, elbow	STV-W G1/8-AG 6	10.08.02.00288



[WWW.SCHMALZ.COM/10.07.06.00500](http://WWW.SCHMALZ.COM/10.07.06.00500)