




VSL 4-2 PU MI-TR

Vacuum/compressed air hose VSL is delivered in the desired length.

Available accessories: hose clamp



Design data VSL 4-2 PU MI-TR

Technical data

Attribute	Value
Material hose	PU
Bending radius min.	20.0 mm
Color	Milky-transparent
Length max.	50.00 m
Pressure range (operating pressure) [bar]	-0.95 ... 10.00 bar
Operating temperature	-40 ... 60 °C
Outside diameter D	4.00 mm
Internal diameter d	2.00 mm

Design data

Attribute	Value
Outside diameter D	4.00 mm
Internal diameter d	2.00 mm

Art.-Nr.: 10.07.09.00001

**Technical data**

Attribute	Value
Material hose	PU
Bending radius min.	20.0 mm
Length max.	50.00 m
Pressure range (operating pressure) [bar]	-0.95 ... 10.00 bar
Operating temperature	-40 ... 60 °C
Weight / Meter	0.011 kg/m
Product family	VSL
Design hose type	4-2

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.09.00001

**Ordering Data Accessories 10.07.09.00001**

Typ		Item number
Plug union, straight	STV-GE G1/4-AG 4	10.08.02.00203
Plug union, straight	STV-GE G1/8-AG 4	10.08.02.00202
Plug union, straight	STV-GE M5-AG 4	10.08.02.00200
Plug union, straight	STVI-GE G1/4-IG 4	10.08.02.00152
Plug union, straight	STVI-GE G1/8-IG 4	10.08.02.00149
Plug union, T	STV-T G1/8-AG 4	10.09.02.00039
Plug union, T	STV-T M5-AG 4	10.09.02.00038
Plug union, elbow	STV-W G1/4-AG 4	10.08.02.00157
Plug union, elbow	STV-W G1/8-AG 4	10.08.02.00156
Plug union, elbow	STV-W M5-AG 4	10.08.02.00155
Plug union, elbow	STV-WF G1/4-AG 4	10.08.02.00167
Plug union, elbow	STV-WF G1/8-AG 4	10.08.02.00166
Plug union, elbow	STV-WF M5-AG 4	10.08.02.00165
Plug connector, T	SVB-T 4	10.09.02.00020

