




VSL 6-4 PU MI-TR

Vacuum/compressed air hose VSL is delivered in the desired length.

Available accessories: hose clamp



Design data VSL 6-4 PU MI-TR

Technical data

Attribute	Value
Material hose	PU
Bending radius min.	35.0 mm
Color	Milky-transparent
Length max.	500.00 m
Pressure range (operating pressure) [bar]	-0.95 ... 10.00 bar
Operating temperature	-20 ... 90 °C
Outside diameter D	6.00 mm
Internal diameter d	4.00 mm

Design data

Attribute	Value
Outside diameter D	6.00 mm
Internal diameter d	4.00 mm

Art.-Nr.: 10.07.09.00002

**Technical data**

Attribute	Value
Material hose	PU
Bending radius min.	35.0 mm
Length max.	500.00 m
Pressure range (operating pressure) [bar]	-0.95 ... 10.00 bar
Operating temperature	-20 ... 90 °C
Weight / Meter	0.016 kg/m
Product family	VSL
Design hose type	6-4

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.09.00002

**Ordering Data Accessories 10.07.09.00002**

Typ		Item number
Hose sleeve	ST G1/8-AG 4 M5-ROH	10.08.03.00153
Hose sleeve	ST M5-AG 4 M5-V	10.08.03.00152
Plug union, straight	STV-GE G1/4-AG 6	10.08.02.00205
Plug union, straight	STV-GE G1/8-AG 6	10.08.02.00204
Plug union, straight	STV-GE G1/8-AG 6 HT	10.08.02.00389
Plug union, straight	STV-GE M5-AG 6	10.08.02.00201
Plug union, straight	STVI-GE G1/4-IG 6	10.08.02.00153
Plug union, straight	STVI-GE G1/8-IG 6	10.08.02.00150
Plug union, T	STV-T G1/4-AG 6	10.09.02.00042
Plug union, T	STV-T G1/8-AG 6	10.09.02.00040
Plug union, elbow	STV-W G1/4-AG 6	10.08.02.00159
Plug union, elbow	STV-W G1/8-AG 6	10.08.02.00288
Plug union, elbow	STV-W G1/8-AG 6	10.08.02.00158
Plug union, elbow	STV-W G1/8-AG 6 HT	10.08.02.00391
Plug union, elbow	STV-W M5-AG 6	10.08.02.00296
Plug union, elbow	STV-W M5-AG 6	10.08.02.00235
Plug union, elbow	STV-W M5-AG 6 HT	10.08.02.00397
Plug union, elbow	STV-WF G1/4-AG 6	10.08.02.00169
Plug union, elbow	STV-WF G1/8-AG 6	10.08.02.00168
Plug connector, T	SVB-T 6	10.09.02.00021

