

Art.-Nr.: 10.07.09.00005


**Technical data**

Attribute	Value
Material hose	PVC with tissue
Color	Clear-transparent
Length max.	50.00 m
Pressure range (operating pressure) [bar]	bar
Operating temperature	°C
Outside diameter D	15.00 mm
Internal diameter d	9.00 mm

VSL 15-9 PVC-G KL-TR

Vacuum/compressed air hose VSL is delivered in the desired length.

Available accessories: hose clamp



Design data VSL 15-9 PVC-G KL-TR

Design data

Attribute	Value
Outside diameter D	15.00 mm
Internal diameter d	9.00 mm



Art.-Nr.: 10.07.09.00005

**Technical data**

Attribute	Value
Material hose	PVC with tissue
Length max.	50.00 m
Pressure range (operating pressure) [bar]	bar
Operating temperature	°C
Weight / Meter	0.144 kg/m
Product family	VSL
Design hose type	15-9

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.09.00005

**Ordering Data Accessories 10.07.09.00005**

Typ		Item number
Hose clamp	SSB 10-16 ST-VZ	10.07.10.00001
Cap (rectangular)	KAPP 9 Band	20.12.01.00036
Hose sleeve	ST G1/2-AG 9 MS-V	10.08.03.00161
Hose sleeve	ST G1/4-AG 9 MS-V	10.08.03.00157
Hose sleeve	ST G1/8-AG 9 MS-V	10.08.03.00155
Hose sleeve	ST G3/8-AG 9 MS-V	10.08.03.00159

