


Art.-Nr.: 10.07.09.00006


**Technical data**

Attribute	Value
Material hose	PVC with tissue
Color	Clear-transparent
Length max.	50.00 m
Pressure range (operating pressure) [bar]	bar
Operating temperature	°C
Outside diameter D	21.00 mm
Internal diameter d	12.00 mm

VSL 21-12 PVC-G KL-TR

Vacuum/compressed air hose VSL is delivered in the desired length.

Available accessories: hose clamp

**Design data**

Attribute	Value
Outside diameter D	21.00 mm
Internal diameter d	12.00 mm

Design data VSL 21-12 PVC-G KL-TR



Art.-Nr.: 10.07.09.00006

**Technical data**

Attribute	Value
Material hose	PVC with tissue
Length max.	50.00 m
Pressure range (operating pressure) [bar]	bar
Operating temperature	°C
Weight / Meter	0.297 kg/m
Design hose type	21-12

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.09.00006

**Ordering Data Accessories 10.07.09.00006**

Typ		Item number
Hose clamp	SSB 12-22 ST-VZ	10.07.10.00160
Hose clamp	SSB 16-27 ST-VZ	10.07.10.00002
Hose clamp	SSB 20-32 ST-VZ	10.07.10.00003
Cap (rectangular)	KAPP 9 Band	20.12.01.00036
Hose sleeve	ST G1/2-AG 13 MS-V	10.08.03.00162
Hose sleeve	ST G1/4-AG 13 MS-V	10.08.03.00158
Hose sleeve	ST G3/4-AG 13 MS-V	10.08.03.00164
Hose sleeve	ST G3/8-AG 13 MS-V	10.08.03.00160

