


Technical data

Attribute	Value
Material hose	PVC with wire spiral
Bending radius min.	85.0 mm
Color	Clear-transparent
Length max.	50.00 m
Pressure range (operating pressure) [bar]	-0.90 ... 5.00 bar
Operating temperature	-15 ... 65 °C
Outside diameter D	26.00 mm
Internal diameter d	19.00 mm

VSL 26-19 PVC-DS KL-TR

Vacuum/compressed air hose VSL is delivered in the desired length.

Available accessories: hose clamp



Design data

Attribute	Value
Outside diameter D	26.00 mm
Internal diameter d	19.00 mm

Design data VSL 26-19 PVC-DS KL-TR

Art.-Nr.: 10.07.09.00007

**Technical data**

Attribute	Value
Material hose	PVC with wire spiral
Bending radius min.	85.0 mm
Length max.	50.00 m
Pressure range (operating pressure) [bar]	-0.90 ... 5.00 bar
Operating temperature	-15 ... 65 °C
Weight / Meter	0.330 kg/m
Product family	VSL
Design hose type	26-19

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.09.00007

**Ordering Data Accessories 10.07.09.00007**

Type		Item number
Hose clamp	SSB 20-32 ST-VZ	10.07.10.00003
Cap (rectangular)	KAPP 9 Band	20.12.01.00036
Hose sleeve	ST G1/2-AG 19 MS-V	10.08.03.00163
Hose sleeve	ST G3/4-AG 19 MS-V	10.08.03.00165

