




Teknik veriler

Attribute	Value
Malzeme hortumu	PE
Renk	mavi
Uzunluk maks.	100,00 m
Basınç aralığı (çalışma basıncı) [bar]	bar
Çalışma sıcaklığı	°C
Dış çap D	4,00 mm
İç çap d	2,00 mm

VSL 4-2 PE BL

Vakum/basıncılı hava hortumu VSL istenilen uzunlukta teslim edilir.

Mevcut aksesuarlar: hortum kelepçesi



Tasarım verileri

Attribute	Value
Dış çap D	4,00 mm
İç çap d	2,00 mm

Tasarım verileri VSL 4-2 PE BL



Basıncılı hava hortumu
VSL 4-2 PE BL



Art.-Nr.: 10.07.09.00013



Teknik veriler

Attribute	Value
Malzeme hortumu	PE
Uzunluk maks.	100,00 m
Basınç aralığı (çalışma basıncı) [bar]	bar
Çalışma sıcaklığı	°C
Ağırlık / Metre	0,087 kg/m
Ürün ailesi	VSL
Tasarım hortum tipi	4-2

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.09.00013



Sipariş Verisi Aksesuarlar 10.07.09.00013

Typ		Ürün numarası
Otomatik rakor, düz	STV-GE G1/4-AG 4	10.08.02.00203
Otomatik rakor, düz	STV-GE G1/8-AG 4	10.08.02.00202
Otomatik rakor, düz	STV-GE M5-AG 4	10.08.02.00200
Otomatik rakor, düz	STVI-GE G1/4-IG 4	10.08.02.00152
Otomatik rakor, düz	STVI-GE G1/8-IG 4	10.08.02.00149
Fiş birleşimi, T	STV-T G1/8-AG 4	10.09.02.00039
Fiş birleşimi, T	STV-T M5-AG 4	10.09.02.00038
Tapa rakoru, dirsek	STV-W G1/4-AG 4	10.08.02.00157
Tapa rakoru, dirsek	STV-W G1/8-AG 4	10.08.02.00156
Tapa rakoru, dirsek	STV-W M5-AG 4	10.08.02.00155
Tapa rakoru, dirsek	STV-WF G1/4-AG 4	10.08.02.00167
Tapa rakoru, dirsek	STV-WF G1/8-AG 4	10.08.02.00166
Tapa rakoru, dirsek	STV-WF M5-AG 4	10.08.02.00165
Fiş konnektörü, T	SVB-T 4	10.09.02.00020



WWW.SCHMALZ.COM/10.07.09.00013