

Compressed-air hose
VSL 6-4 PE BL



Art.-Nr.: 10.07.09.00014




Technical data

Attribute	Value
Material hose	PE
Color	blue
Length max.	100.00 m
Pressure range (operating pressure) [bar]	bar
Operating temperature	°C
Outside diameter D	6.00 mm
Internal diameter d	4.00 mm

VSL 6-4 PE BL

Vacuum/compressed air hose VSL is delivered in the desired length.

Available accessories: hose clamp



Design data

Attribute	Value
Outside diameter D	6.00 mm
Internal diameter d	4.00 mm

Design data VSL 6-4 PE BL



WWW.SCHMALZ.COM/10.07.09.00014

Compressed-air hose

VSL 6-4 PE BL



Art.-Nr.: 10.07.09.00014



Technical data

Attribute	Value
Material hose	PE
Length max.	100.00 m
Pressure range (operating pressure) [bar]	bar
Operating temperature	°C
Weight / Meter	0.145 kg/m
Product family	VSL
Design hose type	6-4

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.09.00014



Ordering Data Accessories 10.07.09.00014

Typ		Item number
Hose sleeve	ST G1/8-AG 4 M5-ROH	10.08.03.00153
Hose sleeve	ST M5-AG 4 M5-V	10.08.03.00152
Plug union, straight	STV-GE G1/4-AG 6	10.08.02.00205
Plug union, straight	STV-GE G1/8-AG 6	10.08.02.00204
Plug union, straight	STV-GE G1/8-AG 6 HT	10.08.02.00389
Plug union, straight	STV-GE M5-AG 6	10.08.02.00201
Plug union, straight	STVI-GE G1/4-IG 6	10.08.02.00153
Plug union, straight	STVI-GE G1/8-IG 6	10.08.02.00150
Plug union, T	STV-T G1/4-AG 6	10.09.02.00042
Plug union, T	STV-T G1/8-AG 6	10.09.02.00040
Plug union, elbow	STV-W G1/4-AG 6	10.08.02.00159
Plug union, elbow	STV-W G1/8-AG 6	10.08.02.00158
Plug union, elbow	STV-W G1/8-AG 6	10.08.02.00288
Plug union, elbow	STV-W G1/8-AG 6 HT	10.08.02.00391
Plug union, elbow	STV-W M5-AG 6	10.08.02.00235
Plug union, elbow	STV-W M5-AG 6	10.08.02.00296
Plug union, elbow	STV-W M5-AG 6 HT	10.08.02.00397
Plug union, elbow	STV-WF G1/4-AG 6	10.08.02.00169
Plug union, elbow	STV-WF G1/8-AG 6	10.08.02.00168
Plug connector, T	SVB-T 6	10.09.02.00021



WWW.SCHMALZ.COM/10.07.09.00014