

Vacuum hose (meter)

VSL 19-13 PVC-DS KL-TR



Art.-Nr.: 10.07.09.00016




Technical data

| | |
|---|----------------------|
| Material hose | PVC with wire spiral |
| Bending radius min. | 85.0 mm |
| Color | Clear-transparent |
| Length max. | 50.00 m |
| Pressure range (operating pressure) [bar] | -0.90 ... 5.00 bar |
| Operating temperature | -15 ... 65 °C |
| Outside diameter D | 19.20 mm |
| Internal diameter d | 13.00 mm |

VSL 19-13 PVC-DS KL-TR

Vacuum/compressed air hose VSL is delivered in the desired length.

Available accessories: hose clamp



Design data

| | |
|---------------------|----------|
| Outside diameter D | 19.20 mm |
| Internal diameter d | 13.00 mm |

Design data VSL 19-13 PVC-DS KL-TR



WWW.SCHMALZ.COM/10.07.09.00016

1

Art.-Nr.: 10.07.09.00016

**Technical data**

| | |
|---|----------------------|
| Material hose | PVC with wire spiral |
| Bending radius min. | 85.0 mm |
| Length max. | 50.00 m |
| Pressure range (operating pressure) [bar] | -0.90 ... 5.00 bar |
| Operating temperature | -15 ... 65 °C |
| Weight / Meter | 0.190 kg/m |
| Product family | VSL |
| Design hose type | 19-13 |

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

**Ordering Data Accessories 10.07.09.00016**

| Typ | | Item number |
|-------------|--------------------|----------------|
| Hose clamp | SSB 12-20 ST-VZ | 10.07.10.00159 |
| Hose clamp | SSB 16-27 ST-VZ | 10.07.10.00002 |
| Hose sleeve | ST G1/2-AG 13 MS-V | 10.08.03.00162 |
| Hose sleeve | ST G1/4-AG 13 MS-V | 10.08.03.00158 |
| Hose sleeve | ST G3/4-AG 13 MS-V | 10.08.03.00164 |
| Hose sleeve | ST G3/8-AG 13 MS-V | 10.08.03.00160 |

