


Vakum hortumu (metre)

VSL 60-50 PU-DS-AS KL-TR



Art.-Nr.: 10.07.09.00020




VSL 60-50 PU-DS-AS KL-TR

Vakum/basıncılı hava hortumu VSL istenilen uzunlukta teslim edilir.

Mevcut aksesuarlar: hortum kelepçesi

Teknik veriler

Attribute	Value
Malzeme hortumu	PU, tel spiral, antistatik
Bükme yarıçapı dak	35,0 mm
Renk	Şeffaf-açık
Uzunluk maks.	20,00 m
Basınç aralığı (çalışma basıncı) [bar]	-0,82 ... 2,48 bar
Çalışma sıcaklığı	-40 ... 90 °C
Dış çap D	60,00 mm
İç çap d	50,00 mm



Tasarım verileri VSL 60-50 PU-DS-AS KL-TR

Tasarım verileri

Attribute	Value
Dış çap D	60,00 mm
İç çap d	50,00 mm



WWW.SCHMALZ.COM/10.07.09.00020

Art.-Nr.: 10.07.09.00020

**Teknik veriler**

Attribute	Value
Malzeme hortumu	PU, tel spiral, antistatik
Bükme yarıçapı dak	35,0 mm
Uzunluk maks.	20,00 m
Basınç aralığı (çalışma basıncı) [bar]	-0,82 ... 2,48 bar
Çalışma sıcaklığı	-40 ... 90 °C
Ürün ailesi	VSL
Tasarım hortum tipi	60-50

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.09.00020

**Sipariş Verisi Aksesuarlar 10.07.09.00020**

Typ	Ürün numarası
Hortum kelepçesi	SSD 57-62 ST-VZ
	10.07.10.00036

WWW.SCHMALZ.COM/10.07.09.00020