




VSL 48-38 PU-DS-AS TR

Vacuum/compressed air hose VSL is delivered in the desired length.

Available accessories: hose clamp



Design data VSL 48-38 PU-DS-AS TR

Technical data

Attribute	Value
Material hose	PU, wire spiral, antistatic
Bending radius min.	29.0 mm
Color	Transparent
Length max.	20.00 m
Pressure range (operating pressure) [bar]	-1.00 ... 3.12 bar
Operating temperature	-40 ... 90 °C
Outside diameter D	48.00 mm
Internal diameter d	38.00 mm

Design data

Attribute	Value
Outside diameter D	48.00 mm
Internal diameter d	38.00 mm

Art.-Nr.: 10.07.09.00031

**Technical data**

Attribute	Value
Material hose	PU, wire spiral, antistatic
Bending radius min.	29.0 mm
Length max.	20.00 m
Pressure range (operating pressure) [bar]	-1.00 ... 3.12 bar
Operating temperature	-40 ... 90 °C
Weight / Meter	0.520 kg/m
Product family	VSL
Design hose type	48-38

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.09.00031

**Ordering Data Accessories 10.07.09.00031**

Type		Item number
Hose clamp	SSD 42-46 ST-VZ	10.07.10.00156
Hose clamp	SSD 43-48 ST-VZ	10.07.10.00020
Hose sleeve	ST G1-1/2-AG 38 MS-V	10.08.03.00170

