




VSL 61-50 PVC-DS GR

Vacuum/compressed air hose VSL is delivered in the desired length.

Available accessories: hose clamp



Design data VSL 61-50 PVC-DS GR

## Technical data

| Attribute                                 | Value                |
|-------------------------------------------|----------------------|
| Material hose                             | PVC with wire spiral |
| Bending radius min.                       | 90.0 mm              |
| Color                                     | grey                 |
| Length max.                               | 10.00 m              |
| Pressure range (operating pressure) [bar] | -0.78 ... 1.50 bar   |
| Operating temperature                     | -20 ... 70 °C        |
| Outside diameter D                        | 61.00 mm             |
| Internal diameter d                       | 50.00 mm             |

## Design data

| Attribute           | Value    |
|---------------------|----------|
| Outside diameter D  | 61.00 mm |
| Internal diameter d | 50.00 mm |

Art.-Nr.: 10.07.09.00033

**Technical data**

| Attribute                                 | Value                |
|-------------------------------------------|----------------------|
| Material hose                             | PVC with wire spiral |
| Bending radius min.                       | 90.0 mm              |
| Length max.                               | 10.00 m              |
| Pressure range (operating pressure) [bar] | -0.78 ... 1.50 bar   |
| Operating temperature                     | -20 ... 70 °C        |
| Weight / Meter                            | 0.541 kg/m           |
| Product family                            | VSL                  |
| Design hose type                          | 61-50                |

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

**Further documentation**

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.07.09.00033](http://www.schmalz.com/10.07.09.00033)

**Ordering Data Accessories 10.07.09.00033**

| Typ        | Item number                    |
|------------|--------------------------------|
| Hose clamp | SSD 57-62 ST-VZ 10.07.10.00036 |

