





VSL 71-60 PU-DS-AS TR

Vacuum/compressed air hose VSL is delivered in the desired length.

Available accessories: hose clamp



Design data VSL 71-60 PU-DS-AS TR

Technical data

Attribute	Value
Material hose	PU, wire spiral, antistatic
Bending radius min.	40.0 mm
Color	Transparent
Length max.	20.00 m
Pressure range (operating pressure) [bar]	-0.69 ... 2.09 bar
Operating temperature	-40 ... 90 °C
Outside diameter D	71.00 mm
Internal diameter d	60.00 mm

Design data

Attribute	Value
Outside diameter D	71.00 mm
Internal diameter d	60.00 mm

Art.-Nr.: 10.07.09.00034

**Technical data**

Attribute	Value
Material hose	PU, wire spiral, antistatic
Bending radius min.	40.0 mm
Length max.	20.00 m
Pressure range (operating pressure) [bar]	-0.69 ... 2.09 bar
Operating temperature	-40 ... 90 °C
Weight / Meter	0.780 kg/m
Product family	VSL
Design hose type	71-60

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.09.00034

**Ordering Data Accessories 10.07.09.00034**

Typ	Item number
Hose clamp	SSD 65-70 ST-VZ
	10.07.10.00098

