

Vacuum hose (meter)

VSL 12-9 PU MI-TR



Art.-Nr.: 10.07.09.00037




Technical data

Material hose	PU
Bending radius min.	70.0 mm
Color	Milky-transparent
Length max.	50.00 m
Pressure range (operating pressure) [bar]	-0.95 ... 10.00 bar
Operating temperature	-20 ... 90 °C
Outside diameter D	12.00 mm
Internal diameter d	9.00 mm

VSL 12-9 PU MI-TR

Vacuum/compressed air hose VSL is delivered in the desired length.

Available accessories: hose clamp



Design data

Outside diameter D	12.00 mm
Internal diameter d	9.00 mm

Design data VSL 12-9 PU MI-TR



WWW.SCHMALZ.COM/10.07.09.00037

1

Art.-Nr.: 10.07.09.00037

**Technical data**

Material hose	PU
Bending radius min.	70.0 mm
Length max.	50.00 m
Pressure range (operating pressure) [bar]	-0.95 ... 10.00 bar
Operating temperature	-20 ... 90 °C
Weight / Meter	0.058 kg/m
Product family	VSL
Design hose type	12-9

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

**Ordering Data Accessories 10.07.09.00037**

Typ		Item number
Hose clamp	SSB 10-16 ST-VZ	10.07.10.00001
Hose sleeve	ST G1/2-AG 9 MS-V	10.08.03.00161
Hose sleeve	ST G1/4-AG 9 MS-V	10.08.03.00157
Hose sleeve	ST G1/8-AG 9 MS-V	10.08.03.00155
Hose sleeve	ST G3/8-AG 9 MS-V	10.08.03.00159
Plug union, straight	STV-GE G1/2-AG 12	10.08.02.00210
Plug union, straight	STV-GE G1/4-AG 12	10.08.02.00208
Plug union, straight	STV-GE G3/8-AG 12	10.08.02.00209
Plug union, T	STV-T G1/4-AG 12	10.09.02.00045
Plug union, elbow	STV-W G1/2-AG 12	10.08.02.00164
Plug union, elbow	STV-W G1/4-AG 12	10.08.02.00162
Plug union, elbow	STV-W G3/8-AG 12	10.08.02.00163
Plug connector, T	SVB-T 12	10.09.02.00023

