




VSL 33-25 PVC-DS KL-TR

Vacuum/compressed air hose VSL is delivered in the desired length.

Available accessories: hose clamp



Design data VSL 33-25 PVC-DS KL-TR

Technical data

Attribute	Value
Material hose	PVC with wire spiral
Bending radius min.	95.0 mm
Color	Clear-transparent
Length max.	50.00 m
Pressure range (operating pressure) [bar]	-0.85 ... 4.00 bar
Operating temperature	-15 ... 65 °C
Outside diameter D	33.00 mm
Internal diameter d	25.00 mm

Design data

Attribute	Value
Outside diameter D	33.00 mm
Internal diameter d	25.00 mm

Art.-Nr.: 10.07.09.00041

**Technical data**

Attribute	Value
Material hose	PVC with wire spiral
Bending radius min.	95.0 mm
Length max.	50.00 m
Pressure range (operating pressure) [bar]	-0.85 ... 4.00 bar
Operating temperature	-15 ... 65 °C
Weight / Meter	0.510 kg/m
Product family	VSL
Design hose type	33-25

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.09.00041

**Ordering Data Accessories 10.07.09.00041**

Type		Item number
Hose clamp	SSB 23-35 ST-VZ	10.07.10.00161
Hose clamp	SSB 32-50 ST-VZ	10.07.10.00004
Cap (rectangular)	KAPP 9 Band	20.12.01.00036
Hose sleeve	ST G1-AG 25 MS-V	10.08.03.00167
Hose sleeve	ST G3/4-AG 25 MS-V	10.08.03.00166

