

Vakum hortumu (metre)

VSL 85-75 PVC-PS GR



Art.-Nr.: 10.07.09.00048



VSL 85-75 PVC-PS GR

Vakum/basıncılı hava hortumu VSL istenilen uzunlukta teslim edilir.


Mevcut aksesuarlar: hortum kelepçesi

Teknik veriler

Attribute	Value
Malzeme hortumu	PVC-spiralli PVC
Bükme yarıçapı dak	114,0 mm
Renk	gri
Uzunluk maks.	10,00 m
Basınç aralığı (çalışma basıncı) [bar]	-0,29 ... 1,00 bar
Çalışma sıcaklığı	-20 ... 70 °C
Dış çap D	85,00 mm
İç çap d	75,00 mm

Tasarım verileri

Attribute	Value
Dış çap D	85,00 mm
İç çap d	75,00 mm



Tasarım verileri VSL 85-75 PVC-PS GR



WWW.SCHMALZ.COM/10.07.09.00048

Art.-Nr.: 10.07.09.00048

**Teknik veriler**

Attribute	Value
Malzeme hortumu	PVC-spiralli PVC
Bükme yarıçapı dak	114,0 mm
Uzunluk maks.	10,00 m
Basınç aralığı (çalışma basıncı) [bar]	-0,29 ... 1,00 bar
Çalışma sıcaklığı	-20 ... 70 °C
Ağırlık / Metre	0,920 kg/m
Ürün ailesi	VSL
Tasarım hortum tipi	85-75

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.09.00048

**Sipariş Verisi Aksesuarlar 10.07.09.00048**

Typ	Ürün numarası
Hortum kelepçesi	SSD 85-90 ST-VZ
	10.07.10.00102

WWW.SCHMALZ.COM/10.07.09.00048