




VSL 85-75 PVC-PS GR

Vacuum/compressed air hose VSL is delivered in the desired length.

Available accessories: hose clamp



Design data VSL 85-75 PVC-PS GR

Technical data

Attribute	Value
Material hose	PVC with PVC-spiral
Bending radius min.	114.0 mm
Color	grey
Length max.	10.00 m
Pressure range (operating pressure) [bar]	-0.29 ... 1.00 bar
Operating temperature	-20 ... 70 °C
Outside diameter D	85.00 mm
Internal diameter d	75.00 mm

Design data

Attribute	Value
Outside diameter D	85.00 mm
Internal diameter d	75.00 mm

Art.-Nr.: 10.07.09.00048

**Technical data**

Attribute	Value
Material hose	PVC with PVC-spiral
Bending radius min.	114.0 mm
Length max.	10.00 m
Pressure range (operating pressure) [bar]	-0.29 ... 1.00 bar
Operating temperature	-20 ... 70 °C
Weight / Meter	0.920 kg/m
Product family	VSL
Design hose type	85-75

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.09.00048

**Ordering Data Accessories 10.07.09.00048**

Typ	Item number
Hose clamp	SSD 85-90 ST-VZ 10.07.10.00102

