


Compressed-air hose
VSL 12-9 PE BL



Art.-Nr.: 10.07.09.00050




Technical data

Material hose	PE
Color	blue
Length max.	100.00 m
Pressure range (operating pressure) [bar]	bar
Operating temperature	°C
Outside diameter D	12.00 mm
Internal diameter d	9.00 mm

VSL 12-9 PE BL

Vacuum/compressed air hose VSL is delivered in the desired length.

Available accessories: hose clamp



Design data

Outside diameter D	12.00 mm
Internal diameter d	9.00 mm

Design data VSL 12-9 PE BL



WWW.SCHMALZ.COM/10.07.09.00050

Compressed-air hose
VSL 12-9 PE BL



Art.-Nr.: 10.07.09.00050



Technical data

Material hose	PE
Length max.	100.00 m
Pressure range (operating pressure) [bar]	bar
Operating temperature	°C
Weight / Meter	0.457 kg/m
Product family	VSL
Design hose type	12-9

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!



Ordering Data Accessories 10.07.09.00050

Typ		Item number
Hose clamp	SSB 10-16 ST-VZ	10.07.10.00001
Hose sleeve	ST G1/2-AG 9 MS-V	10.08.03.00161
Hose sleeve	ST G1/4-AG 9 MS-V	10.08.03.00157
Hose sleeve	ST G1/8-AG 9 MS-V	10.08.03.00155
Hose sleeve	ST G3/8-AG 9 MS-V	10.08.03.00159
Plug union, straight	STV-GE G1/2-AG 12	10.08.02.00210
Plug union, straight	STV-GE G1/4-AG 12	10.08.02.00208
Plug union, straight	STV-GE G3/8-AG 12	10.08.02.00209
Plug union, T	STV-T G1/4-AG 12	10.09.02.00045
Plug union, elbow	STV-W G1/2-AG 12	10.08.02.00164
Plug union, elbow	STV-W G1/4-AG 12	10.08.02.00162
Plug union, elbow	STV-W G3/8-AG 12	10.08.02.00163
Plug connector, T	SVB-T 12	10.09.02.00023



WWW.SCHMALZ.COM/10.07.09.00050