




VSL 49-38 PU-DS-AS TR HD

Vacuum/compressed air hose VSL is delivered in the desired length.

Available accessories: hose clamp



Design data VSL 49-38 PU-DS-AS TR HD

Technical data

Attribute	Value
Material hose	PU, wire spiral, antistatic
Bending radius min.	104.0 mm
Color	Transparent
Length max.	15.00 m
Pressure range (operating pressure) [bar]	-1.00 ... 4.47 bar
Operating temperature	-20 ... 90 °C
Outside diameter D	49.00 mm
Internal diameter d	38.00 mm

Design data

Attribute	Value
Outside diameter D	49.00 mm
Internal diameter d	38.00 mm

Art.-Nr.: 10.07.09.00052

**Technical data**

Attribute	Value
Material hose	PU, wire spiral, antistatic
Bending radius min.	104.0 mm
Length max.	15.00 m
Pressure range (operating pressure) [bar]	-1.00 ... 4.47 bar
Operating temperature	-20 ... 90 °C
Weight / Meter	0.790 kg/m
Product family	VSL
Design hose type	49-38

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.09.00052

**Ordering Data Accessories 10.07.09.00052**

Type		Item number
Hose clamp	SSD 43-48 ST-VZ	10.07.10.00020
Hose clamp	SSD 45-50 ST-VZ	10.07.10.00157
Hose sleeve	ST G1-1/2-AG 38 MS-V	10.08.03.00170

