


Vakum hortumu (metre)

VSL 71-60 PU-DS-AS TR HD

Art.-Nr.: 10.07.09.00065




VSL 71-60 PU-DS-AS TR HD

Vakum/basıncılı hava hortumu VSL istenilen uzunlukta teslim edilir.

Mevcut aksesuarlar: hortum kelepçesi

Teknik veriler

Attribute	Value
Malzeme hortumu	PU, tel spiral, antistatik
Bükme yarıçapı dak	156,0 mm
Renk	Şeffaf
Uzunluk maks.	15,00 m
Basınç aralığı (çalışma basıncı) [bar]	-1,00 ... 2,92 bar
Çalışma sıcaklığı	-40 ... 90 °C
Dış çap D	71,00 mm
İç çap d	60,00 mm



Tasarım verileri VSL 71-60 PU-DS-AS TR HD

Tasarım verileri

Attribute	Value
Dış çap D	71,00 mm
İç çap d	60,00 mm



WWW.SCHMALZ.COM/10.07.09.00065

Art.-Nr.: 10.07.09.00065

**Teknik veriler**

Attribute	Value
Malzeme hortumu	PU, tel spiral, antistatik
Bükme yarıçapı dak	156,0 mm
Uzunluk maks.	15,00 m
Basınç aralığı (çalışma basıncı) [bar]	-1,00 ... 2,92 bar
Çalışma sıcaklığı	-40 ... 90 °C
Ağırlık / Metre	1,180 kg/m
Ürün ailesi	VSL
Tasarım hortum tipi	71-60

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.09.00065

**Sipariş Verisi Aksesuarlar 10.07.09.00065**

Typ	Ürün numarası
Hortum kelepçesi	SSD 65-70 ST-VZ
	10.07.10.00098

WWW.SCHMALZ.COM/10.07.09.00065