

Vacuum hose (meter)

## VSL 10-7 PE MI-TR



Art.-Nr.: 10.07.09.00083




### Technical data

Material hose	PE
Bending radius min.	60.0 mm
Color	Milky-transparent
Length max.	50.00 m
Pressure range (operating pressure) [bar]	-0.95 ... 10.00 bar
Operating temperature	-30 ... 70 °C
Outside diameter D	10.00 mm
Internal diameter d	7.00 mm

VSL 10-7 PE MI-TR

Vacuum/compressed air hose VSL is delivered in the desired length.

Available accessories: hose clamp



### Design data

Outside diameter D	10.00 mm
Internal diameter d	7.00 mm

Design data VSL 10-7 PE MI-TR



[WWW.SCHMALZ.COM/10.07.09.00083](http://WWW.SCHMALZ.COM/10.07.09.00083)

1

Art.-Nr.: 10.07.09.00083

**Technical data**

Material hose	PE
Bending radius min.	60.0 mm
Length max.	50.00 m
Pressure range (operating pressure) [bar]	-0.95 ... 10.00 bar
Operating temperature	-30 ... 70 °C
Weight / Meter	0.370 kg/m
Product family	VSL
Design hose type	10-7

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

**Ordering Data Accessories 10.07.09.00083**

Typ		Item number
Hose clamp	SSB 8-12 ST-VZ	10.07.10.00158
Hose clamp	SSB 10-16 ST-VZ	10.07.10.00001
Plug union, straight	STV-GE G1/2-AG 10	10.08.02.00253
Plug union, straight	STV-GE G1/4-AG 10	10.08.02.00251
Plug union, straight	STV-GE G3/8-AG 10	10.08.02.00252
Plug union, straight	STVI-GE G1/4-IG 10	10.08.02.00260
Plug union, T	STV-T G1/4-AG 10	10.09.02.00044
Plug union, elbow	STV-W G1/2-AG 10	10.08.02.00256
Plug union, elbow	STV-W G1/4-AG 10	10.08.02.00254
Plug union, elbow	STV-W G3/8-AG 10	10.08.02.00255
Plug union, elbow	STV-WF G1/4-AG 10	10.08.02.00258
Plug union, elbow	STV-WF G1/8-AG 10	10.08.02.00257
Plug union, elbow	STV-WF G3/8-AG 10	10.08.02.00259
Plug connector, T	SVB-T 10	10.09.02.00025

